



WECK VISISTAT

Skin Stapler

AT A GLANCE

- see-through window
- patented non-stop feed action
- pre-cock function for exact staple positioning
- sharper staples
- tall staples
- 3 removers

STRENGTH AND CONTROL

Teleflex's WECK Visistat skin stapler meets both needs, the surgeon's for a safe and easy-to-use instrument and the patient's for quick recovery. Each disposable Visistat skin stapler is loaded with 35 either regular or wide medical grade stainless steel staples that can be used in a wide range of surgical procedures.

The precision instrument features a see-through window for better visibility and a patented non-stop feed mechanism for easy release and reduced jamming.

Thanks to sharper staples, an easy and less traumatic penetration of the tissue can be effected. Finally, even their removal turns out to become a less painful procedure, due to their tallness.




The WECK Visistat is perfectly supplemented by our WECK removers, providing both strength and reliability.





- ① see-through window
- ② patented non-stop feed
- ③ 35 medical grade stainless steel staples

VISISTAT SKIN STAPLER			WECK
	REF.	DESCRIPTION	QTY
	WK528235	35W (wide)	6
	WK528135	35R (regular)	6

REMOVER			WECK
	REF.	DESCRIPTION	QTY
	WK525960	stainless steel	36
	WK525970	plastic, brown	6
	WK525980	plastic, white	12

DISTRIBUTED BY:
TELEFLEX HEADQUARTERS INTERNATIONAL, IRELAND · Teleflex Medical Europe Ltd. · IDA Business & Technology Park
 Dublin Road · Athlone · Co Westmeath · Tel. +353 (0)9 06 46 08 00 · Fax +353 (0)14 37 07 73 · orders.intl@teleflex.com
UNITED KINGDOM Tel. +44 (0)14 94 53 27 61 · info.uk@teleflex.com
SOUTH AFRICA Tel. +27 (0)11 807 4887 · assist.africa@teleflex.com
WWW.TELEFLEX.COM
 94 05 96 - 00 00 01 · REV A · 1015 0.5 · All data current at time of printing. Subject to technical changes without further notice.